

Product information

48 11 J1

Precision Circlip Pliers

For internal circlips in bore holes

DIN 5256 C



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Bolted joint: precise, zero backlash operation of pliers
- Non-slip plastic coating on the handles
- Straight tips
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened

C



General	
Article No.	48 11 J1
EAN	4003773048527
Pliers	grey atramentized
Handles	with non-slip plastic coating
Weight	105 g
Dimensions	140 x 48 x 12 mm
Standard	DIN 5256 C
Reach	no
RohS	no

Technical details		
Size of bore	Ø 12 – 25 mm	
Tips (diameter)	Ø 1.3 mm	

Classification		
eCl@ss 5.1.4	21040301	
ETIM 5.0	EC002228	
ETIM 6.0	EC002228	
proficl@ss 6.0	AAC470c002	
UNSPSC 13.1	27112140	

technical change and errors excepted