

Product information

86 05 250 T

Pliers Wrench

Pliers and a wrench in a single tool







- Replaces the need for sets of metric and imperial spanners
- Smooth jaws for damage free installation of plated fittings working directly on chrome!
- Pliers with tether attachment point for mounting a fall protection system
- Also excellent for gripping, holding, pressing and bending workpieces
- Zero backlash jaw pressure prevents damage to edges of sensitive components
- Fast adjustment by pushing a button directly on the workpiece
- No unintentional shift of the gripping jaws and no slipping of the joint
- Parallel jaws give a more solid grip, its design allows flexible adjustment of all widths up to the specified maximum size
- The ratchet type principle allows quick and easy tightening and release of all bolted connections
- Lever transmission greater than 10: 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened

General	
Article No.	86 05 250 T
EAN	4003773080138
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Weight	500 g
Dimensions	250 x 58 x 23 mm
Reach	no
RohS	no

Technical details	
Jaw thickness (joint) (B2)	8.0 mm
Joint thickness (B3)	14.0 mm
Tips thickness (B1)	8.0 mm
Adjustment positions	19
Capacities for nuts	Ø 2 Inch
Capacities for nuts	52 mm



KNIPEX Quality – Made in Germany



Classification	
eCl@ss 5.1.4	21043826
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112
Accessories	
86 09 250 V01	Protective jaws for 86 XX 250, 3 pairs
Spare Parts	
87 09 01	Assortment of spare parts for adjustment for 86/87 XX 250/300 (without 87 2X XXX),

technical change and errors excepted