

Product information

87 26 250

KNIPEX Cobra® VDE

High-tech Water Pump Pliers, insulated

DIN ISO 8976 IEC 60900 DIN EN 60900



- Adjustment by sliding one jaw directly on to the workpiece: fast, reliable and comfortable handling
- Fine adjustment: allows optimum adjustment to differently sized workpieces and comfortable handle position
- Good access to the workpiece due to slim size of head and joint area
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	87 26 250
EAN	4003773071495
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested
Weight	340 g
Dimensions	250 x 59 x 20 mm
Standard	DIN ISO 8976 DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Adjustment positions	24
Capacities for pipes (diameter)	Ø 2 Inch
Capacities for nuts	46 mm
Capacity for pipes, inches (diameter)	Ø 50 mm
VDE tested	yes

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112

Spare Parts

87 09 01	Assortment of spare parts for adjustment for 86/87 XX 250/300 (without 87 2X XXX),
87 29 01	range of spare parts for 87 2X-250,

Spare Parts

87 29 01

range of spare parts for 87 2X-250,

technical change and errors excepted



Just push the pliers handle to adjust!



Quick setting without using a push-button

