

## Product information

# 90 22 01 SB

## KNIPEX TwistCut® Corrugated Pipe Cutter



### Fast and safe cutting of corrugated plastic pipes

- For the reliable and fast cutting of many plastic corrugated pipes with the universal capacity range from Ø 13 to 32 mm
- For corrugated plastic pipes with ridge widths of up to 2.7 mm
- No damage to the internal cables or pipes
- Separate even softer, flexible plastic corrugated pipes: Apply little pressure on the TwistCut® when cutting to avoid the corrugated pipe to be deformed
- Simple insertion, reliable and easy cutting without waste
- Precise cut without damage thanks to unique arrangement of the cutters with side guide
- Good accessibility thanks to slim design
- Made of glass fibre reinforced multi-component plastic with soft gripping zone

MM

General	
Article No.	90 22 01 SB
EAN	4003773082286
Weight	47 g
Dimensions	100 x 86 x 38 mm
Reach	no
RohS	no

Technical details	
Cutting capacities (diameter)	Ø 13 – 32 mm

Classification	
eCl@ss 5.1.4	21040601
ETIM 5.0	EC000148
ETIM 6.0	EC000148
proficl@ss 6.0	AAB927c006
UNSPSC 13.1	23151901

*technical change and errors excepted*



Convenient handling due to fastener with locking device and opening by means of internal spring



Also for protective pipes on aluminium composite pipes in plumbing, up to Ø 32 mm



Clean cutting edge with no damage to internal cables as the cut is always at the top of the corrugation



Easy handling: press the KNIPEX TwistCut® together, twist it with a little pressure, and you're done!





