

Product information

95 32 340 SR

ACSR Cable Cutter

(ratchet action)

For cables with a steel core



Superior cutting performance with low power input

- The cable cutter cuts through ACSR cable with a steel core (= Aluminium Conductor Steel Reinforced) up to Ø 32 mm
- With one- or two-handed operation, the high leverage guarantees a simple, accurate cut
- Handy and compact with highest performance
- Extremely stable, dual guided of the revolving blade
- No fanning out of the cable: precision-ground and induction-hardened cutting edge for a clean cut and long service life
- Low handforce required due to two-stage gear drive with ratchet mechanism
- Fixed handle with support area for putting down the pliers when cutting
- Locking mechanism for transporting with safely closed handles
- All wearing parts are available as spare parts and exchangeable
- Special high grade tool steel, multi stage oil-hardened

MM



General

Article No.	95 32 340 SR
EAN	4003773081241
Shears	burnished
Handles	with multi-component grips
Weight	1,310 g
Dimensions	340 x 135 x 30 mm
Reach	no
RohS	no

Technical details

Diameter	32 mm
Inch diameter	Ø 1 1/4 Inch
MCM	477

Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001
UNSPSC 13.1	23241616

Spare Parts

95 39 340 01	Pivot cutter repair kit for 95 32 340 SR,
--------------	---

technical change and errors excepted



Enormous power with a weight of just 1300 g



The strong "flange" on the handle can be used as a practical support surface when cutting larger diameters