

Product information

97 43 06

Crimp System Pliers

For exchangeable crimping dies



- With attached crimping dies for insulated terminals and plug connectors
- Just one tool for almost 1000 crimping applications
- Almost parallel crimping motion
- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force due to lever action for fatigue-reduced operation
- Ergonomically designed handles
- Different locators for precise positioning of the connectors
- Crimping dies for applications not covered in the range offered here, may be available on request
- Chrome vanadium electric steel in special quality, oil-hardened

General	
Article No.	97 43 06
EAN	4003773031048
Pliers	burnished
Head	burnished
Handles	with multi-component grips
Weight	610 g
Dimensions	200 x 96 x 18 mm
Reach	yes
RohS	no

Technical details	
Applications	Crimp System Pliers for insulated terminals and plug connectors
Capacity in square millimetres	$0.5 - 6.0 \text{ mm}^2$
Number of crimping positions	3
AWG	20 — 10

Classification		
eCl@ss 5.1.4	21040301	
ETIM 5.0	EC000168	
ETIM 6.0	EC000168	
proficl@ss 6.0	AAA946c003	
UNSPSC 13.1	27112147	

technical change and errors excepted