

Product information

97 52 64

Four-Mandrel Crimping Pliers for turned contacts



- Pressure adjustment depending on the conductor's diameter by means of adjusting wheel in 4 different positions
- Locator for positioning the contacts
- For crimping turned contacts
- Four-mandrel crimping for top-quality crimping connections
- Mandrel gauge to check the basic setting
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- High operation comfort thanks to handy shape
- Chrome vanadium electric steel in special quality, oil-hardened

General

Article No.	97 52 64
EAN	4003773044093
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	424 g
Dimensions	180 x 73 x 20 mm
Reach	yes
RohS	no

Technical details



Applications	turned contacts
Capacity in square millimetres	0.08 — 2.5 mm ²
AWG	28 — 14
Number of crimping positions	1
Max. contact diameter	5 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

Spare Parts

97 59 14	Locator for 97 52 14,
----------	-----------------------

technical change and errors excepted