

Product information

97 54 24

Crimping Pliers for micro plugs

Parallel crimping





- Parallel crimping performance to satisfy the particularly high standards of small connectors
- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatiguereduced operation
- Crimping pliers for other mini plugs such as HD 22, Modu IV, Micro Timer, MQS ... on request
- Chrome vanadium electric steel in special quality, oil-hardened

General	
Article No.	97 54 24
EAN	4003773060215
Pliers	burnished
Handles	with multi-component grips
Weight	305 g
Dimensions	190 x 60 x 34 mm
Reach	yes
RohS	no

Technical details		
Applications	D Sub; HD 20; HDE plug	
Capacity in square millimetres	0.03 — 0.56 mm ²	
Number of crimping positions	3	
AWG	32 — 20	

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted

KNIPEX Quality – Made in Germany





