

Product information

97 54 27

Crimping Pliers for micro plugs

Parallel crimping

For MQS connectors without single wire seal

- Parallel crimping performance to satisfy the particularly high standards of small connectors
- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Crimping pliers for other mini plugs such as HD 22, Modu IV, Micro Timer, MQS ... on request
- Chrome vanadium electric steel in special quality, oil-hardened



General

Article No.	97 54 27
EAN	4003773079873
Pliers	burnished
Handles	with multi-component grips
Weight	305 g
Dimensions	190 x 60 x 34 mm
Reach	yes
RohS	no

Technical details



Applications	MQS connector without single wire seal
Capacity in square millimetres	0.25 / 0.35 / 0.5 mm ²
Number of crimping positions	3

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted

