

Product information

98 33 25

Torque Wrench

With driving square, reversible

ISO 3315 IEC 60900 DIN EN 60900

- Transparent insulated scale range 5 - 25 Nm
- Reversible for tightening of lefthanded threads
- Lockable torque adjustment
- Adjustable in steps of 0.25 Nm
- Easy and secure locking of attached sockets due to screw lock
- Calibration certificate included
- Chrome Vanadium steel



⚠ 1000 V 

General

Article No.	98 33 25
EAN	4003773072676
Weight	1,230 g
Dimensions	290 x 85 x 55 mm
Standard	ISO 3315 DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Square drive	3/8
Range of Application	5 - 25 Nm

Classification

eCl@ss 5.1.4	21040223
ETIM 5.0	EC002132
ETIM 6.0	EC002132
proficl@ss 6.0	AAA303c011
UNSPSC 13.1	27111715

Spare Parts

98 33 98	Spare Covering Cap for 98 33 25/50 / 98 43 50,
98 33 99	Square drive 3/8",

technical change and errors excepted