

INTERCHANGEABLE WALL PLUG POWER SUPPLY 24VDC 18WATT

STONTRONICS: SW4466C



Features:

- Interchangeable AC Heads
- 1 Year Warranty
- Level VI Efficiency
- Worldwide Approvals

Description:

The Stontronics range of 18 Watt Interchangeable wall plug power supplies provide 18 Watts of continuous power with the flexibility of worldwide usage as they are supplied with UK, Euro, Auz & USA AC Heads , all Efficiency Level VI and carry worldwide safety approvals.

Specification	
Part Code	SW4466C
Input Voltage Range	90-264 Vac
Input Frequency Range	50/60Hz +/- 3Hz
Input Current Rated	0.5A max.
Input AC Heads	UK, Euro, Auz & USA
Output Voltage Rating	+24V
Output Current Range	0.75A
Output Min Current	0A
Output Connection Type	2.1x5.5x12mm centre positive – Straight
Line and Load Regulation	+/-5%
Ripple & Noise	240mVp-p
Efficiency	85%Min
Over Voltage Protection	auto restart
Over Load Protection	auto restart
Operating Temperature	0°C to +40°C
Storage Temperature	-20°C to +80°C
Operating Humidity	10% to 90%
Storage Humidity	10% to 90%
Hi-Pot	3000VAC 5mA 1min
Leakage Current	<0.25mA max
Safety Standard	UL,CSA,GS,CE,UK,SAA
EMI Standard	FCC part 15: Class B EN 55032, Class B, GB9254, GB17625.1
MTBF	50K Hours
Size mm max.	85.5 X 39.78 X 43.8 mm
Weight	105 g

General Note




TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

STONTRONICS

TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500

INTERCHANGEABLE WALL PLUG POWER SUPPLY 24VDC 18WATT STONTRONICS: SW4466C

Diagrams



General Note
TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.