

NEO MPI 3232



Sample image

Order symbol: NEO MPI 3232

Product nbr: 4850071

Description: Multiperforated plastic mounting plate

Remarks:

Including: Plastic mountingplate

EAN: 6418074314802

El. number:

- Finland: 3424425
- Denmark: 8212098161
- Sweden: 2506229

Dimensions:

	Length	Width	Height
mm:		265	275
inch:		10.43	10.83

Materials:

Material:	ABS
Base colour:	
Cover colour:	
Gasket material:	

Temperatures:

Temperature °C (short term):	
Temperature °C (continuous):	
Temperature °F (short term):	
Temperature °F (continuous):	

Rating:

Ingress protection (EN 60529):	
Impact Resistance (EN 62262):	
Electrical insulation:	Not insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	-
Flammability Rating:	
Glow Wire Test (IEC 695-2-1) °C:	
NEMA Class	

Certificates: