

# NEO MPS 3222



Sample image

**Order symbol:** NEO MPS 3222

**Product nbr:** 4850060

**Description:** Metal mounting plate

**Remarks:**

**Including:** Metal mountingplate

**EAN:** 6418074314765

**El. number:**

- Finland: 3424421
- Denmark: 8212098129
- Sweden: 2506225

NEO MPS 3222.jpg

<b>Dimensions:</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm:	275	165	1.5
inch:	10.83	6.5	0.06

#### **Materials:**

Material: Galvanized steel  
Base colour:  
Cover colour:  
Gasket material:

#### **Temperatures:**

Temperature °C (short term):  
Temperature °C (continuous):  
Temperature °F (short term):  
Temperature °F (continuous):

#### **Rating:**

Ingress protection (EN 60529):  
Impact Resistance (EN 62262):  
Electrical insulation: Not insulated  
Halogen free (DIN/VDE 0472, Part 815): 1  
UV resistance: -  
Flammability Rating:  
Glow Wire Test (IEC 695-2-1) °C: C  
NEMA Class

#### **Certificates:**