

# PMK NEO 30



Sample image

**Order symbol:** PMK NEO 30

**Product nbr:** 4850051

**Description:** Pole mounting kit

**Remarks:**

**EAN:** 6418074314550

**EI. number:**

- Finland: 3424429
- Denmark: 8212098190
- Sweden: 2506232

**Including:** Complete set for pole mounting

Dimensions:	Length	Width	Height
mm:		300	400
inch:		11.81	15.75

## Materials:

Material: Stainless steel

Base colour:

Cover colour:

Gasket material:

## Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

NEMA Class

## Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

## Certificates: