Heavy Duty Connector Housings

multicomp PRO



Specifications

Surface : Powder-Coated
Material : Aluminium Die-Cast

Colour : Grey

Temperature Range : -40°C to +125°C
Locking Type : Single Locking latch
Locking Material : Stainless Steel


Hoods/Housing Sealing : NBR IP Rating : IP65


RoHS Compliant


Housing, Bulkhead Mount



MP009445












MP009446









| Part Number | Description | |
|-------------|---|--|
| MP009445 | Metal, 1 Locking Lever | |
| MP009446 | Metal, 1 Locking Lever with Plastic Cover | |

Housing, Surface Mount



MP009447





Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro





Heavy Duty Connector Housings

multicomp PRO




MP009448









MP009449








MP009450





| Part Number | Description | |
|-------------|--|--|
| MP009447 | Metal, 1 Locking Lever, 2×M32 | |
| MP009448 | Metal, 1 Locking Lever, M40 | |
| MP009449 | Metal, 1 Locking Lever, 2×M32 with Plastic Cover | |
| MP009450 | Metal, 1 Locking Lever, M40 with Plastic Cover | |

Dimensions: Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Page <2>

Heavy Duty Connector Housings



Part Number Table

| Description | Part Number |
|--|-------------|
| Housing, H48B, Metal, Bulkhead Mount, 1 Locking Lever | MP009445 |
| Housing, H48B, Metal, Bulkhead Mount, 1 Locking Lever with Plastic Cover | MP009446 |
| Housing, H48B, Metal, Surface Mount, 1 Locking Lever, 2×M32 | MP009447 |
| Housing, H48B, Metal, Surface Mount, 1 Locking Lever, M40 | MP009448 |
| Housing, H48B, Metal, Surface Mount, 1 Locking Lever, 2×M32 with Plastic Cover | MP009449 |
| Housing, H48B, Metal, Surface Mount, 1 Locking Lever, M40 with Plastic Cover | MP009450 |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

