# Heavy Duty Cable Glands multicomp PRO



## RoHS **Compliant**




#### **Specifications**

**Body Material** : Nylon : NBR Sealing Material

Degree of Protection : IP68 (with O-searing)

: -40°C to +100°C (Short-term +120°C) Temperature Range

### **Diagram**



Part Number	Thread Size	SW1 Wrench Size	ØC Clamping Range	AG Thread Diameter	GL Thread Length	Weight g
MP009453	M20×1.5	24	5-10	20	9	10.3
MP009454	M25×1.5	33	13-18	25	11	19
MP009455	M32×1.5	42	18-25	32	11	38
MP009456	M40×1.5	51	22-32	40	13	65

#### Part Number Table

Description	Part Number	
Plastic Cable Gland, M20, Nylon, Black	MP009453	
Plastic Cable Gland, M25, Nylon, Black	MP009454	
Plastic Cable Gland, M32, Nylon, Black	MP009455	
Plastic Cable Gland, M40, Nylon, Black	MP009456	

**Dimensions: Millimetres** 

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

