



Four-way cable tie entry for easy orientation of wires and cables. These mounts can be applied with a #6 screw or with user supplied adhesive.

Part Number: ABM100-S6-C
Product Family: 4-Way Mounts Without Adhesive
Product Line: Screw Mounts

Product Line: Screw/Rivet Applied

Product Line: Specialty Mounts with User Supplied Adhesives

RoHS Compliancy Status: Compliant

Part Description: 4-Way Cable Tie Mounts Without Adhesive

Product Type: Cable Tie Mounts - User Supplied Adhesive

Material: Nylon 6.6

Color: White

UL Recognized: E136577

Height (In.): .20

Height (mm): 5.1

Length (In.):	1.00
Length (mm):	25.4
Width (In.):	1.00
Width (mm):	25.4
Adhesive Type:	User supplied adhesive and/or (2) #6 (M3) screws
CE Compliant:	CT-ACC1 / 10.96
Environment:	Indoors
Flammability Rating:	UL94 V-2
Metric Screw Size:	M3
Mounting Method:	User Supplied Adhesive and/or Countersunk #6 (M3) Screw
Screw Size:	#6 (M3)
Std. Pkg. UOM:	PK
Used With Cable Ties:	M, I, S
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100