



- Used with *PANDUIT*® cable ties for a complete wire routing solution
- Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
- Tear tab provides fast and easy liner removal to speed installation
- For indoor use

‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Ties.

\* Flame retardant products are manufactured from a material that is rated UL94V-0.

Part Number: ABMT-S6-Q20  
Product Family: *Tak-Ty*® Hook & Loop Cable Tie Mounts- Screw Applied  
Product Line: Screw/Rivet Applied

RoHS Compliancy Status: Compliant

Part Description: Screw applied mount for use with *Tak-Ty*® Hook & Loop Cable Ties.

Material: Nylon 6.6

Color: Black

Height (In.): .34

Height (mm): 8.4

Length (In.):	1.12
Length (mm):	28.5
Width (In.):	1.10
Width (mm):	28.6
Environment:	Indoors
Flammability Rating:	UL94 V-2
Marker Diameter (In.):	null
Metric Screw Size:	M3
Mounting Method:	# 6 (M3) Screw
Screw Size:	#6 (M3)
Std. Pkg. UOM:	PK
Used With Cable Ties:	Tak-Ty® Hook & Loop Cable Ties (HLM, HLS, HLT & TTS)
UOM:	PC
Std. Pkg. Qty.:	25
Min. Order Qty.:	25