

# CREALITY

MPN - SERMOON V1

Description – Sermoon V1 has a fully-enclosed structure with no wire or high-temp parts exposure

## Sermoon V1 & V1 Pro 3D Printer



Printing Noise Lower Than 45dB

Built-in WiFi

Out-of-Box Printing

## Specifications

<b>Print Technology:</b> FDM	<b>Nozzle Diameter:</b> Standard 0.4mm
<b>Max. Build Dimensions:</b> 175*175*165mm	<b>Nozzle Quantity:</b> 1 piece
<b>Machine Dimensions:</b> 400*380*430mm	<b>Supported Filament:</b> PLA/ABS/PETG/TPU
<b>Package Dimensions:</b> 485*465*526mm	<b>Filaments Diameter:</b> 1.75mm
<b>Machine Weight:</b> 11.5kg	<b>User Interface:</b> 4.3" Color Touch Screen
<b>Package Gross Weight:</b> 15kg	<b>Rated Power:</b> 150W
<b>Extruder:</b> Sprite Direct Drive	<b>Resume Print:</b> Yes
<b>Max. Nozzle Temperature:</b> ≤250°C	<b>Filament Detection:</b> Yes
<b>Max. Heated Bed Temperature:</b> ≤80°	<b>Print Interface:</b> Wi-Fi / SD Card
<b>Print Precision:</b> ±0.1mm	<b>Intelligent Door:</b> Yes (V1 Pro)
<b>Layer Thickness:</b> 0.1-0.4mm	<b>Built-In Live Camera:</b> Yes (V1 Pro)
<b>Power Supply:</b> 100-120Vac 200-240Vac 50/60Hz	