

# CREALITY

MPN - HALOT-LITE

Description –Large Format Resin 3D Printer

## HALOT-LITE Resin 3D Printer



Precision integral light source

Efficient and easy slicing

Efficient and easy slicing High preformanic mainboard

# Product Parameters

LCD Pixel: 3840\*2400

LCD Screen: 8.9" monochrome

Light Source: Integral Light Source

Printing size: 192\*120\*200mm

XY-axis precision: 0.05mm

Printing speed: 1-4s/layer

Interaction Screen: 5" color touch screen

Input power: 100-240V

Machine Weight: 10.6kg

Layer Thickness: 0.01-0.2mm

Material: 405nm UV Resin

Auto-leveling: Easy manual leveling

Machine size: 330\*301\*572mm