

# TM 2330



Sample image

**Order symbol:** TM 2330

**Product nbr:** 9512019

**Description:** Back Panel. for enclosures:

**Remarks:** 300x230x87.  
300x230x110

**Including:**

**EAN:** 6418074034083

**El. number:**

- Finland: 3423929
- Denmark: 8212004074
- Sweden: 2536169

<b>Dimensions:</b>	<b>Length</b>	<b>Width</b>	<b>Height</b>
mm:		274	221
inch:		10.79	8.7

**Materials:**

Material:

Base colour:

Cover colour:

Gasket material:

**Rating:**

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

NEMA Class

**Temperatures:**

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

**Certificates:**