2.0 USB Adapter Type A Plug to Receptacle

pro-**signal**



Features

RoHS **Compliant**

- Projects 21mm from ports when connected
- Dimensions (HxWxD): 28mm × 17mm × 34mm

Specification

Connector Side A : Type A Plug Connector Side B : Type A Receptacle

USB Type

All cable 100% test : open, short, miss wire.


: 2Ω max.


Resistance

: $100M\Omega$ min. Insulation Resistance

Hi-top

: 300V DC/10ms.





Pin Assignment

P1		P2	
1	Red	1	
2	White	2	
3	Green	3	
4	Black	4	

1	1007 - 26AWG BC Wire	PCS	4
2	USB2.0AM Nickle plated	PCS	1
3	USB2.0AF Nickle plated	PCS	1
4	Inner modual PE (LDPE)	G	1.5
5	Black PVC	G	3

Part Number Table

Description	Part Number	
2.0 USB Adapter, Type A Plug to Receptacle	PSG91064	

Dimensions: Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence, pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

