



[Home](#) > [Products](#) > [IT & Business](#) > [Print Solutions](#) > **Faxes**



Faxes

SF6800

Description

Corporate Laser Fax

Features

- Paper:
- Engine - Laser
- Fax:
- Memory Size (Pages) - 400
- Quick Scan - 3 sec's
- Copy/Print:
- Print Speed (Mono/Colour) - up to 8ppm/-** (see specification)


Specification

- Engine - Laser
- Auto Document Feeder (Sheets) - 50
- Paper Supply/Option - 250/250
- Fax:
- Modem (Kbps)/TX Speed - approx 14.4/6 sec's*
- Memory Size (Pages) - 400
- Direct/PC - Direct
- Auto Fax/Tel Switch - Yes
- Quick Scan - 3 sec's
- Delay Send - Yes
- Handset/On-Hook Dial - Yes
- Speed Dial - 20+150
- Alpha Dialling (Phone Book) - Yes
- Auto Redial - Yes
- Dual Access - Yes
- Battery Back-Up - Max. 7 days
- Copy/Print:
- Multi Copy (pages) - 99
- Copy Collection (123,123) - Yes
- Print Speed (Mono/Colour) - up to 8ppm/-**
- Greyscales - 64
- Reduction/Enlargement - 50-200%
- Consumables:
- Consumable Product Code - SF-6800D6
- Standard Page Yield (5% Coverage) - approx 6000***
- Ink Save Mode - Yes
- Size:
- Dimensions (WxDxH mm) - 386x405x270
- Additional Features - Priority TX, Image TX report, Low toner alert, Help button
- * Condition: Standard Resolution, MMR (JBIG), 33,6Kbps, Phase "C" by ITU-T No1 Chart, Memory Tx, ECM.
- ** Print Speed will be affected by Operating System used, computing performance, application

software, connecting method, media type, media size and job complexity.

- *** Yield may be affected by operating environment, printing interval, colour/black, media type and media size.

 Print This Page

 Close