


| Model | L(mm) |
|---------|---------|
| AV29889 | 1500±50 |
| AV29890 | 3000±50 |

PIN Assignment

| P1 | P2 |
|-------|-------|
| 1 | 1 |
| 2 | 2 |
| 3 | 3 |
| 4 | 4 |
| 5 | 5 |
| 6 | 6 |
| SHELL | SHELL |



NOTE:

- 1.CABLE:0. 10CU*10*6C+1/0. 32BC+AL+0D5. 0,BLACK COLOR ,PVC JACKET.
- 2.CONNECTORS:6 PIN MINI DIN*2PCS
- 3.MOLD ASSEMBLY,BLACK COLOR
- 4.OPEN/SHORT TEST:100% TEST.
- 5.ROHS COMPLIANT

| | | | | | | | | | |
|----------|------------|------------|--|--------------|-----------------------------|----------|--------|------|------|
| Customer | | | | Product name | 6 PIN MINI DIN PLUG TO PLUG | Material | Colour | Unit | View |
| Design | Technology | | | Model | 29889-29890 | | | | |
| Check | Standard | | | Drawing No | | | | | |
| Approve | Date | 2022.03.05 | | | | | | | |