

SRT1807**115-07189**

The Elasticity of the SRT ties makes them suitable for use in many applications.



Manufactured from a soft, tear-resistant thermoplastic polyurethane these ties have several unique features: UV and weather resistant, strong yet elastic, and suitable for temperatures as low as -40 degrees C. The SRT ties are releasable and reusable which is ideal for bundling cables in temporary applications such as musical events, theatres, cable harnesses.

The SRT range offers solutions to numerous bundling applications. The soft, flexible material makes these ties particularly suitable for use on data and fibre-optic cables. The elasticity of the material makes them ideal for securing young trees to support poles, and other applications within the gardening and landscaping industry.

Base Data**Colour**

Black (BK)

Package Content

50

Quantity (Sold Unit / EDP)

50

Short Description

The elasticity of the tie means that in applications such as securing trees, it is not necessary to loosen the tie and re-tighten it as frequently as with other products - the tie will grow with the tree.

Logisitic and Packaging**Carton Quantity**

50

EAN code

4031026108551

Quantity of Europallet

60000

Weight (kg) (Metric)

2.2 kg

Material and Specifications**Flammability**

UL94 HB

Material

Thermoplastic Polyurethane (TPU)

Material Shortcut

TPU

Operating Temperature (Metric)

-40 °C to +85 °C

ROHS Conformity

TRUE

Product Dimensions**Bundle Diameter max (Metric)**

45

Length L (Metric)

180

Minimum Tensile Strength (N)

57

Width W (Metric)

7

