

United Kingdom

SRT34011



The Elasticity of the SRT ties makes them suitable for use in many applications.





115-11349

Manufactured from a soft, tear-resistant thermoplastic polyurethane these ties have several unique features: UV and weather resistant, strong yet elastic, and suitable for temperatures as low as -40 degrees C. The SRT ties are releasable and reusable which is ideal for bundling cables in temporary applications such as musical events, theatres, cable harnesses.

The SRT range offers solutions to numerous bundling applications. The soft, flexible material makes these ties particularly suitable for use on data and fibre-optic cables. The elasticity of the material makes them ideal for securing young trees to support poles, and other applications within the gardening and landscaping industry.

Base Data

Colour

Black (BK)

Label E-Number Norway

13 451 53

Package Content

50

Quantity (Sold Unit / EDP)

50

Short Description

The elasticity of the tie means that in applications such as securing trees, it is not necessary to loosen the tie and re-tighten it as frequently as with other products - the tie will grow with the tree.

Logisitic and Packaging

Carton Quantity

0

EAN code

4031026108582

Quantity of Europallet

18000

Weight (kg) (Metric)

8.65 kg

Material and Specifications

Flammability

UL94 HB

Material

Thermoplastic Polyurethane (TPU)

Material Shortcut

TPU

Operating Temperature (Metric)

-40 °C to +85 °C

ROHS Conformity

TRUE

Product Dimensions

Bundle Diameter max (Metric)

90

Length L (Metric)

340

Minimum Tensile Strength (N)

123

Width W (Metric)

11

1 of 2 16/08/2006 15:15

© HellermannTyton 2006

2 of 2