

T50SSBS50TE**155-30602**

Offering the "soft-push" technology, this inside serrated tie is mounted on the top of the stud. The additional height gained by this design gives a clear "stand-off" from the panel.

The T50SSBS50TE allows very precise routing of cable bundles.

**Base Data****Colour**

Black (BK)

Package Content

500

Quantity (Sold Unit / EDP)

500

Logisitic and Packaging**Carton Quantity**

5000

EAN code

4031026218540

Quantity of Europallet

60000

Weight (kg) (Metric)

2.3 kg

Material and Specifications**Flammability**

UL94 V2

Material

Polyamide 6.6 Heat Stabilised (PA66HS)

Material Shortcut

PA66HS

Operating Temperature (Metric)

-40 °C to +105 °C Continuous, (+145 °C for 500 h)

ROHS Conformity

TRUE

Product Dimensions**Bundle Diameter max (Imperial)**

1.38 "

Bundle Diameter max (Metric)

35 mm

Bundle Diameter min (Imperial)

.197 "

Bundle Diameter min (Metric)

5 mm

Length L (Imperial)

6.30 "

Length L (Metric)

160 mm

Minimum Tensile Strength (imperial)

45

Minimum Tensile Strength (N)

200 N

Stud Length Max (Imperial)

.65 "

Stud Length Max (Metric)

16.5 mm

Stud Size (Imperial)

.20 "

Stud Size (Metric)

5 mm

Width W (Imperial)

.181 "

Width W (Metric)

4.6

© HellermannTyton 2006