USB-C to eSATA Cable - For External Storage Devices - USB 3.0 (5Gbps) - 3 ft. (1 m)

Product ID: USB3C2ESAT3

This USB-C to eSATA cable is an external drive adapter that gives you quick and easy access to an eSATA storage device through the USB-C or Thunderbolt 3 port on your laptop.

Even if your laptop doesn't have eSATA ports, the USB 3.0 to eSATA cable makes it easy to connect it to an external storage device. The cable supports connections to standard SATA hard drives (HDD) and solid-state drives (SSD).

The cable also supports connections to optical drives (ODD), enabling you to connect a CD-ROM or DVD-ROM drive to your laptop.

The cable supports eSATA commands and functions such as SMART self-monitoring. It's also compatible with eSATA drive management hardware and software, such as backup utility software.

When connected to a storage device housing HDD or SSD drives, the USB-C to eSATA cable lets IT professionals connect to drives for:

• Data recovery

• Repairing failing drives

• Re-using or re-purposing old drives

• Running drive diagnostics

• Disk imaging

• Backing up and archiving drives to prevent data loss

• Transferring content between the drive and the laptop

The 1-meter cable lets you set up anywhere, enabling you to perform any one of these tasks in a lab, at someone's desk or out in the field. With plug-and-play installation, it's easy to connect on any operating system, without any extra software to install.

USB3C2ESAT3 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

• Connect an eSATA storage device to a USB-C or Thunderbolt 3 computer

Features

• Quickly access eSATA external storage devices with an SSD, HDD or ODD drive from a USB-C computer

• Perform drive management tasks

• Set up in a lab, at a desk or out in the field

• Save setup time with plug-and-play installation

• Compatible with SATA I, II and III

• Backward compatible with USB 2.0

Hardware

	Warranty	2 Years
	Bus Type	USB 3.0
	Number of Drives	1
	Compatible Drive Types	eSATA
	Chipset ID	ASMedia - ASM1153E

Performance

	Maximum Data Transfer Rate	5Gbps
	Type and Rate	USB 3.0 - 5 Gbit/s
	UASP Support	No
	TRIM Support	No
	4Kn Support	Yes

S.M.A.R.T. Support	Yes
Type and Rate	eSATA (6 Gbps)
Port Multiplier	No
Hardware Raid Supported	No
Max Drive Capacity	Currently tested with up to 10TB drives
ATAPI Support	Yes
Hot Swap Capability	Yes
MTBF	1,577,505 hours

Connector(s)

Drive Connectors	eSATA (7 pin, Data)
Host Connectors	USB Type-C (24 pin) USB 3.0 (5Gbps)

Software

OS Compatibility	OS independent; No software or drivers required

Power

Power Source	USB-Powered

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	40%-85%RH

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	36.0 in [91.4 cm]
Product Length	36.0 in [91.4 cm]
Product Width	0.5 in [12.0 mm]
Product Height	0.5 in [12.0 mm]

	Weight of Product	1.6 oz [45.0 g]

Packaging Information

	Package Length	9.8 in [25.0 cm]
	Package Width	1.3 in [34.0 mm]
	Package Height	0.7 in [17.0 mm]
	Shipping (Package) Weight	1.6 oz [45.0 g]

What's in the Box

	Included in Package	adapter cable
		quick-start guide

*Product appearance and specifications are subject to change without notice.