



E32-D11R 2M

Photoelectric sensor, fiber sensor head, diffuse, M6, high flex, 2 m cable

Specifications

Sensing method	Diffuse reflective
Shape	Threaded
Size	M6
Diameter	5.2 mm
Features	Bend resistant, Flexible fiber
Temperature range	-40-70 °C
Sensing distance	820 mm
Cable length	2 m
Bending radius	1 mm

Accessories



E39-F32D 1M

Spiral protective tube for E32, M6, diffuse, optical fibers, 1m



E39-F32D5 0.5M

Spiral protective tube for E32, M6, diffuse, optical fibers, 0.5 m

Related products



E3NX-CA

High-performance color mark sensor



E3NX-CA

High-performance color mark sensor



E3NX-MA

Smart Fiber Amplifier Units



E3NX-FA

High-performance digital fiber amplifier



E3X-NA

Digital fiber amplifier with potentiometer adjustment



E3X-HD

Easy-teach digital fiber amplifier



E3X-SD

Single display digital fiber amplifier

Downloads

CAD Library



Fiber Sensor Selection Selection Guide

EN PDF 51.8 MB

