

Main

Product	Sealed Transformer
Certifications	UL Listed
Type	Mini Power-Zone
Enclosure Code	C
Insulation Temperature	365 °F (185 °C)
Phase	3 phase
Primary Voltage	480 V
Secondary Voltage	208Y/120 V
Full Capacity Taps	2 5 % FCBN
Power Rating	15 kVA
Temperature Rise	115 °C
Winding Material	Copper
Interrupt Rating	18 kA
Circuit Breaker Type	Feeder breaker Primary main breaker Secondary main breaker
Interior Type	QO Load Center interior
Number of Spaces Available	27
Number of Circuits	27
Enclosure Type	NEMA 3R hot-rolled steel

Complementary

Height	45.20 in (1148.08 mm)
Width	27.40 in (695.96 mm)
Depth	13.50 in (342.9 mm)
Product Weight	510.00 lb(US) (231.33 kg)

Ordering and shipping details

GTIN	785901728139
Nbr. of units in pkg.	1
Package weight(Lbs)	550.00 lb(US) (249.476 kg)

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	45.20 in (114.8 cm)
Package 1 width	27.40 in (69.6 cm)
Package 1 Length	13.50 in (34.3 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel (Metallic), which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation

Contractual warranty

Warranty	18 months
----------	-----------