

UK USB C 20W USB Fast Charger with PD (Power Delivery)



TIGER PART: TGR-USB-20W-PD-UK

- Manufactured to work with a massive range of devices including Smart watches and mobile phones
- 3 stage Power Delivery PD charging system

Six Safety Protection System



The Tiger Power range of USB chargers are safety approved and highly reliable, meeting latest level VI energy efficiency legislation. The TGR-USB-20W-PD-UK is designed to power a wide range of devices including those that support super fast charging such as smart watches and mobile phones



Part number (no USB C cable supplied / UK charger only):	TGR-USB-20W-PD-UK
Part number (Supplied with USB C to USB C cable 1 metre) :	TGR-USB-20W-PD-UK-CAB
Part number (Supplied with USB C to USB C cable 2 metre):	TGR-USB-20W-PD-UK-CAB-2M
Input voltage:	100-240vac (230vac nominal)
Input frequency:	50Hz
Output voltage:	5vdc 3A / 9vdc 2.22A / 12vdc 1.67A 3 stage auto fast charge
Current:	3 amps max.
Power :	20W max. Fast Charging via auto detect Power Delivery
Dimensions:	180 x 146 x 64mm
Weight:	100g
AC cord length (where supplied):	n/a
DC cord length:	Not applicable
DC connector:	USB type C
Polarity:	Standard
Efficiency:	89%
Input current RMS Max.:	2.0A
Inrush Current at 230vac:	30A max. at 220vac cold start, max. load
Load regulation:	+ / - 5%
Safety approval:	62368-1
M.T.B.F.:	50,000 hours (MIL-HDBK-217F) at 25 degrees C
Operating temperature:	0°C to + 40°C

TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.