

Product information

97 53 14 SB

Self-Adjusting Crimping Pliers for wire ferrules

With lateral access



- Narrow handle width and improved ergonomics
- Reliable hexagonal crimping of wire ferrules from 0.08 to 16 mm² (AWG 16) by simply turning and setting the adjusting wheel and all twin wire ferrules up to 2 x 10 mm² (AWG 2 x 8)
- Hexagonal compression for confined connection dimensions
- For crimping wire ferrules according to DIN 46228 parts 1 + 4
- Self-adjustment to the size of wire ferrules required
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Handy shape and low weight provide high operation comfort
- Special quality chrome vanadium electric steel, oil-hardened



General

Article No.	97 53 14 SB
EAN	4003773048497
Pliers	burnished
Handles	with multi-component grips
Weight	410 g
Dimensions	180 x 74 x 25 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details

Application	Wire ferrules
Capacity in square millimetres	0.08 — 16 mm ²
Number of crimping positions	1
AWG	28 — 8

technical change and errors excepted







