



Sample photo

**Order symbol:** UL PCT 081607  
**Product nbr:** 7032621  
**Description:** UL Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074052490  
**El. number:**  
**Finland:**  
**Electric No.** 8212032198  
**Denmark:**  
**Electric No. Italy:** 7302025U

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

| Dimensions: | Length | Width | Height |
|-------------|--------|-------|--------|
| mm:         | 80     | 160   | 65     |
| inch:       | 3.1    | 6.3   | 2.6    |

#### Materials:

**Material:** Polycarbonate  
**Base colour:** RAL 7035 -light grey  
**Cover screws material:** Stainless steel  
**Cover colour:** Clear transparent  
**Gasket material:** Polyurethane

#### Temperatures:

**Temperature °C (short term):** -40 ... 120 °C  
**Temperature °C (continuous):** -40 ... 80 °C  
**Temperature °F (short term):** -40 ... 250 °F  
**Temperature °F (continuous):** -40 ... 175 °F

#### Rating:

Ingress Protection (EN 60529): IP66/IP67  
Impact Resistance (EN 62262): IK07/IK08  
Electrical insulation: Totally insulated  
Halogen free (DIN/VDE 0472, Part 815): 1  
UV resistance: UL 508  
Flammability Rating: UL 746C 5"  
UL Type:  
Glow Wire Test (IEC 695-2-1) °C: 960

#### Certificates:

Underwriters Laboratories  
SGS Fimko  
UL Canada  
Gost R

