

Product data sheet

Specifications

SQUARE D

Green Premium™



Industrial control transformer, Type T, 1 phase, 3000VA, 240x480V primary, 120/240V secondary, 50/60Hz

9070T3000D31

Product availability : Stock - Normally stocked in distribution facility

Price* : 2,676.00 USD

Main

Product Type	Industrial Control Transformer
Power Rating	3000 VA
Type	T

Complementary

Number of Phases	1 phase
Power Rating	3000 VA UL 3000 VA CSA 3000 VA NOM 2000 VA
Temperature Rise	115 °C
Electrical Connection	Screw clamp terminals
Height	8.75 in (222.25 mm)
Width	9 in (228.60 mm)
Depth	7.24 in (183.90 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC2

Environment

Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

Ordering and shipping details

Category	16205-9070 T (NOT TF) 3000 - 5000VA
Discount Schedule	CP8
GTIN	785901326311
Nbr. of units in pkg.	1
Package weight(Lbs)	59.50 lb(US) (26.989 kg)

* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	13.30 in (33.782 cm)
Package 1 width	11.70 in (29.718 cm)
Package 1 Length	15.00 in (38.1 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	10 Years
----------	----------