

# Product data sheet

Specifications

**SQUARE** D

**Green Premium™**



## Low voltage transformer accessory, mechanical lug kit, 100A, 1/0 AWG to 14 AWG, 3 lugs

DASKP100

**Product availability : Stock - Normally stocked in distribution facility**

**Price\* : 28.00 USD**

### Main

Product or Component Type	Mechanical lug
Line Rated Current	100 A
Accessory / separate part category	Electrical accessory

### Complementary

Provided equipment	Lug 3, primary AWG 14...AWG 1/0 stranded) Nut 3, Bolt 3,
Material	aluminium
Product destination	Transformer
Quantity per Set	Set of 3

### Ordering and shipping details

Category	16268-LUG KITS
Discount Schedule	PE2
GTIN	785901428541
Nbr. of units in pkg.	1
Package weight(Lbs)	3.20 oz (90.719 g)
Returnability	Yes
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.00 in (2.54 cm)
Package 1 width	5.00 in (12.7 cm)
Package 1 Length	6.00 in (15.24 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>California proposition 65</b>	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>PVC free</b>	Yes
<b>Contractual warranty</b>	
<b>Warranty</b>	18 months