## Pluggable Terminal Block multicomp PRO



#### Description

Euro Blocks are ideal for wire termination applications. These euro blocks are offered with a 2.5mm pitch, vertical orientation, and 20-26 AWG. Various positions are available, ranging from 2-12 circuits.

#### Features

- .098" [2.50mm] pitch
- Position options: 2, 3, 4, 5, 6, 8, 10, or 12 circuits
- · Vertical orientation
- 20-26 AWG
- Green insulator
- Operating voltage: 150V
- Current rating: 5A
- Wire guard design

#### Specifications

#### Material:

Wire guard	: Stainless Steel
Clamp	: Phosphor Bronze, Nickel plated
Insulator color	: Green
Insulator	: PA66, rated UL 94V-0

#### Electrical:

Operation voltage
Current rating
Contact resistance
Insulation resistance

: Stainless Steel : 150V : 5A : 20mΩ max : 500MΩ min @ 500V DC

#### Mechanical:

Wire range Wire strip length : 26-20 AWG, 0.5mm<sup>2</sup> : 8mm

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

#### Applications


- Industrial
- Testing and measurement
- Audio applications
- Communication applications
- HVAC equipment
- Traffic control

# multicomp PRO

### RoHS Compliant

# Pluggable Terminal Block multicomp

#### Diagram



#### **Part Number Table**

Description	Part Number
Pluggable Terminal Block, 150V, 5A, 2.5mm, 2 Pos	MP010255
Pluggable Terminal Block, 150V, 5A, 2.5mm, 3 Pos	MP010256
Pluggable Terminal Block, 150V, 5A, 2.5mm, 4 Pos	MP010257
Pluggable Terminal Block, 150V, 5A, 2.5mm, 5 Pos	MP010258
Pluggable Terminal Block, 150V, 5A, 2.5mm, 6 Pos	MP010259
Pluggable Terminal Block, 150V, 5A, 2.5mm, 8 Pos	MP010260
Pluggable Terminal Block, 150V, 5A, 2.5mm, 10 Pos	MP010261
Pluggable Terminal Block, 150V, 5A, 2.5mm, 12 Pos	MP010262

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability for just contents) is of any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability for such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

**Dimensions : Millimetres** 

