

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0500588100**  
**Status:** **Active**  
**Overview:** PicoBlade Connector System  
**Description:** 1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 28-32 AWG, Bag

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-51021-032-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 510210000-AS-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Application Specification 510210001-AS-000 (PDF)</a>
<a href="#">Product Specification 510211009-PS-000 (PDF)</a>	<a href="#">Packaging Specification 500589200SPK-200 (PDF)</a>
<a href="#">Product Specification 510211010-PS-000 (PDF)</a>	<a href="#">Packaging Specification SPK-50058-001-001 (PDF)</a>
<a href="#">Product Specification 510211024-PS-000 (PDF)</a>	<a href="#">Packaging Specification SPK-50058-001-002 (PDF)</a>
<a href="#">Product Specification PS-51021-009-001 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-51021-024-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-51021-025-001 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	50058
Application	Signal, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<u>PicoBlade Connector System</u>
Packaging Alternative	500588000 (Reel)
Product Name	PicoBlade
UPC	800753719620

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	9.671/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.50-1.00mm
Wire Size AWG	28, 30, 32
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification	510210000-AS-000, 510210001-AS-000
Packaging Specification	500589200SPK-200, SPK-50058-001-001, SPK-50058-001-002
Product Specification	510211009-PS-000, 510211010-PS-000, 510211024-PS-000, PS-51021-009-001, PS-51021-024-001, PS-51021-025-001, PS-51021-032-001
Sales Drawing	500580001-SD-000



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

50058 Series

**Use With**

51021 Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Extraction Tool for Micro-Fit Terminals Hand Crimp Tool for 1.25mm Pitch PicoBlade Receptacle Crimp Terminals, 26-32 AWG	11030043
	2002181900

**Japan**

Description	Product #
Hand Crimp Tool	570685000

This document was generated on 07/25/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**