



Pushing Performance  
Since 1945

## Han TC100-HMC-MC-CRT-25 mm<sup>2</sup>-AU



Part number	09 11 200 6125
Specification	Han TC100-HMC-MC-CRT-25 mm <sup>2</sup> -AU
HARTING eCatalogue	<a href="https://b2b.harting.com/09112006125">https://b2b.harting.com/09112006125</a>

### Identification

Category	Contacts
Series	TC 100
Type of contact	Crimp contact
Features	lead-free

### Version

Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	25 mm <sup>2</sup>
Operating current	≤100 A
Contact resistance	≤0.3 mΩ
Stripping length	19 mm
Limiting temperature	-40 ... +125 °C
Mating cycles with other HMC components	≥10,000

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	HMC gold plated



**Pushing Performance**  
Since 1945

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

## Commercial data

Packaging size	10
Net weight	17.8 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors