

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300640454](#)
Status: **Active**
Overview: [BradPower Cordsets and Receptacles](#)
Description: BradPower D-Size (1 3/8"–M35) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 10 AWG, Black TPE Cable, 4.0m (13.12') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E258922

General

Product Family Industrial Cordsets
Series [130064](#)
Connector End A BradPower D-Size (1 3/8"–M35)
Connector End B BradPower D-Size (1 3/8"–M35)
IP Rating IP67
Material - Contact Copper Alloy
Overview [BradPower Cordsets and Receptacles](#)
Product Name BradPower D-Size
Type Double Ended
UPC 78172546613

Physical

Cable Diameter 13.46mm (.530")
Cable Length 4.0m (13.12')
Color - Cable Jacket Black
Coupling Style Threaded
Gender Female-Male
Keyway Single
LED Indicator No
Material - Cable Jacket TPE
Material - Connector Body TPE
Material - Coupling Nut Anodized Aluminum
Material - Plating Mating Gold
Net Weight 454.000/g
Orientation Straight to Straight
Poles 4
Temperature Range - Operating -20° to +90°C
Wire Size AWG 10
Wire/Cable Type TC-ER

Electrical

Current - Maximum per Contact 32.0A
Voltage - Maximum 600V AC/DC

Material Info

Engineering Number CC4030K17M040G

Reference - Drawing Numbers

Sales Drawing SD-130064-006-001



Series image - Reference only

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

China RoHS

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)
Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant with Exemption 3
RoHS Phthalates	Not Contained

Search Parts in this Series

[130064](#) Series