

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200868045

Status:

Active

Overview:

Brad Nano-Change (M8) Products

Description:

Nano-Change (M8) Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 0.25mm² Black PUR LSOH Cable, 2.0m (6.56') Length



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120086
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	883906389420
Physical	
Cable Diameter	4.10mm (.161")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-coded
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	51.277/g
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-25° to +80°C
Wire Size AWG	24
Wire/Cable Type	UL 21198
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC
Material Info	
Engineering Number	403000H08M020
Reference - Drawing Numbers	
Sales Drawing	1200860594-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)4578-DC (25 June 2020)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of	CER_4000406200_00_000.pdf
Conformity	
ZZCERT_UKCA - Declaration of	CER_4000410292_00_000.pdf
Conformity	

Search Parts in this Series

120086 Series

This document was generated on 07/08/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION