

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300680099](#)
Status: **Active**
Overview: BradPower Cordsets and Receptacles
Description: BradPower D-Size (1 3/8"-M35) 4-Pole Trunk Tee, with 4-Pole BradPower D-Size (1 3/8"-M35) Drop, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E258922

General

Product Family Industrial Tees and Splitters
 Series [130068](#)
 IP Rating IP67
 Overview [BradPower Cordsets and Receptacles](#)
 Product Name BradPower D-Size
 Type Power Tap Tee
 UPC 78172536310

Physical

Drop Connector BradPower D-Size (1 3/8"-M35)
 Drop Gender Female
 Keyway Single
 Left Trunk Connector BradPower D-Size (1 3/8"-M35)
 Left Trunk Gender Female
 Leg 1 Length N/A
 Leg 2 Length N/A
 Material - Cable Jacket N/A
 Material - Connector Body PVC
 Material - Coupling Nut Anodized Aluminum
 Net Weight 458.000/g
 Poles 4
 Right Trunk Connector BradPower D-Size (1 3/8"-M35)
 Right Trunk Gender Male
 Temperature Range - Operating -20°C to +90°C

Electrical

Current - Maximum per Contact 32.0A
 Voltage - Maximum 600V AC/DC

Material Info

Engineering Number TC40C40-200G

Reference - Drawing Numbers

Sales Drawing SD-130068-023-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000383479_00_000.pdf

Search Parts in this Series

[130068 Series](#)