Power Lead

multicomp PRO

RoHS

Compliant



Specifications

Connector to Connector Current Rating Voltage Rating Cable Length Jacket Colour : Mains Plug, Euro to IEC 60320 C13 : 10A : 250V AC : 2.5m : Black

Standards

EPA method 3050B : 1996 other acid digestion

BSEN1122 : 2001 method B other acid digestion

EPA method 3052B : 1996 other acid digestion

EPA method 3060 and EPA 7196A : 1992

Atomic absorption spectrometer / inductively coupled plasma atomic emission spectrometer (ICP+AES) UV - VIS spectrophotometer


End 1 : Schuko plug right angled black

Fuse : N / A

Lead : 250 mts HO5 VV-F 3 × 100 black

End 2 : IEC cold connector (C13) black

Diagram



Part Number Table

Description	Part Number
Lead, Euro to Bare, Black, 2.5m	SH10193R

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for which are any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

