RoHS

Compliant




## Features


- UK Plug Top
- DOE Level VI Efficiency
- Overcurrent Protection
- Short Circuit Protection
- 1 Year Warranty
- DC Cable Length: 1500mm

## **Specification**

Models		MP009250	MP009252	MP009254	MP009256
Output	DC Voltage	5V DC	9V DC	12V DC	24V DC
	Rated Current	1amp	0.6amp	0.5amp	0.25amp
	Current Range	0-1amp	0-0.6amp	0-0.5amp	0-0.25amp
	Rated Power	6 Watt			
	Ripple & Noise	200mVp-p max			
	Output Regulation	±5%			
	Output Connector	2.1 × 5.5 × 12mm C+ve			
Input	Voltage Range	90V AC to 264V AC			
	Frequency Range	47Hz to 63Hz			
	Input Current	1.2amp Max			
	Inrush Current	40amp Max			
	Standby Power	0.1W Max			
	Leakage Current	0.25amp Max			
	Input Connector	UK			
Environment	Operating Temp	0°C to 40°C			
	Cooling	Convection			
	Temperature Coefficient	0.05%/°C			
	Humidity	5~95%RH (non-condensing)			
	Storage Temp	-20°C to +80%°C			
Safety & EMC	Safety Standards	CE EN62368-1			
	EMC Emissions	EN55032,EN55035, EN61000-3-2 2014, EN61000-3-3 2013			

## **Mechanical Specification**





**Dimensions : Millimetres** 

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage resulting from any reliance on the Information or use of it (including liability for its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

