



01123608

## Aluminium Enclosure Standard

120 x 360 x 81 mm

Aluminium Enclosure Standard 120 x 360 x 81 mm

[Catalogues](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)
[Assignmentplan](#)
[Terminal Mounting](#)

## Technical data

Height	120 mm
Width	360 mm
Depth	81 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Silver gray (RAL 7001)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-40 °C
temperature max.	90 °C
Seal material	PU (polyurethane) (standard)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Smoke gas concentration	HL 3
Other versions on request	EMV, SBG, SWB, SBGL
Special colours on request	TRUE
Approvals	Lloyd Register, Maritime Register, UL 508A

## Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	85369095
Weight	2.04
GTIN	4250157900203

## ETIM classification

ETIM 8	EC000058
--------	----------

ROSE SYSTEMTECHNIK GMBH  
Erbeweg 13-15  
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0  
Fax: +49 571 50 41-6  
Mail: [rose@rose-pw.de](mailto:rose@rose-pw.de)

## Accessories



**10011009**  
Mounting plate for 01.123608



**10027001**  
HINGE EXTERNAL / GREY



**10061425**  
DIN rail 35/7,5 for xx.163609



**10062003**  
Earth rail for 01.163609