



01142009

Aluminium Enclosure Standard

140 x 200 x 91 mm

Aluminium Enclosure Standard 140 x 200 x 91 mm

[Catalogues](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)
[Assignmentplan](#)
[Terminal Mounting](#)

Technical data

Height	140 mm
Width	200 mm
Depth	91 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Silver gray (RAL 7001)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-40 °C
temperature max.	90 °C
Seal material	PU (polyurethane) (standard)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Smoke gas concentration	HL 3
Other versions on request	EMV, SBG, SWB, SBGL
Special colours on request	TRUE
Approvals	Lloyd Register, Maritime Register, UL 508A

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	85369095
Weight	1.66
GTIN	4250157900227

ETIM classification

ETIM 8	EC000058
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



10011028
Mounting plate for 01.142009



10027001
HINGE EXTERNAL / GREY



10061455
DIN rail 35/7,5 for 01.142009



10062008
Earth rail for 01.232011