



01234023

## Aluminium Enclosure Standard

230 x 400 x 225 mm

Aluminium Enclosure Standard 230 x 400 x 225 mm

[Catalogues](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)
[Assignmentplan](#)
[Terminal Mounting](#)

## Technical data

Height	230 mm
Width	400 mm
Depth	225 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Silver gray (RAL 7001)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-40 °C
temperature max.	90 °C
Seal material	PU (polyurethane) (standard)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Smoke gas concentration	HL 3
Other versions on request	EMV, SBG, SWB, SBGL
Special colours on request	TRUE
Approvals	Lloyd Register, Maritime Register, UL 508A

## Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	76169990
Weight	7.97
GTIN	4250157900364

## ETIM classification

ETIM 8	EC000058
--------	----------

## Accessories



**10011018**  
Mounting plate for 01.234011



**10022001**  
HINGE INTERNAL / STEEL



**10027001**  
HINGE EXTERNAL / GREY



**10061427**  
DIN rail 35/7,5 for xx.234011



**10062011**  
Earth rail for 01.234011