



01236011

Aluminium Enclosure Standard

230 x 600 x 111 mm

Aluminium Enclosure Standard 230 x 600 x 111 mm

[Catalogues](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)
[Assignmentplan](#)
[Terminal Mounting](#)

Technical data

Height	230 mm
Width	600 mm
Depth	111 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Silver gray (RAL 7001)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-40 °C
temperature max.	90 °C
Seal material	PU (polyurethane) (standard)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Smoke gas concentration	HL 3
Other versions on request	EMV, SBG, SWB, SBGL
Special colours on request	TRUE
Approvals	Lloyd Register, Maritime Register, UL 508A

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	85369095
Weight	7.29
GTIN	4250157900371

ETIM classification

ETIM 8	EC000058
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



10011019
Mounting plate for 01.236011



10022001
HINGE INTERNAL / STEEL



10027001
HINGE EXTERNAL / GREY



10061428
DIN rail 35/7,5 for xx.236011



10062012
Earth rail for 01.236011