



02080808

Polyester Enclosure Standard

75 x 80 x 75 mm

Polyester Enclosure Standard 75 x 80 x 75 mm

[Catalogues](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)
[Assignmentplan](#)
[Terminal Mounting](#)

Technical data

Height	75 mm
Width	80 mm
Depth	75 mm
Material	Polyester
Colour	Squirrel Gray (RAL 7000)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK08
temperature min.	-40 °C
temperature max.	90 °C
Seal material	CR-(Chloroprene)
Insulation	Fully insulated according to VDE 0100
Toxicity	Halogen free
Surface resistance	>10 ¹² Ohm
Surface resistance norm	IEC 60093
Special colours on request	TRUE
Approvals	Lloyd Register, Maritime Register, UL 508A

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	39269097
Weight	0.371
GTIN	4250157900500

ETIM classification

ETIM 8	EC000058
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



10061003

DIN rail 15 for 01.080806