



02162609

Polyester Enclosure Standard

160 x 260 x 91 mm

Polyester Enclosure Standard 160 x 260 x 91 mm

[Catalogues](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)
[Assignmentplan](#)
[Terminal Mounting](#)

Technical data

Height	160 mm
Width	260 mm
Depth	91 mm
Material	Polyester
Colour	Squirrel Gray (RAL 7000)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-40 °C
temperature max.	90 °C
Seal material	CR-(Chloroprene)
Insulation	Fully insulated according to VDE 0100
Toxicity	Halogen free
Surface resistance	>10 ¹² Ohm
Surface resistance norm	IEC 60093
Special colours on request	TRUE
Approvals	Lloyd Register, Maritime Register, UL 508A

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	39269097
Weight	1.756
GTIN	4250157900678

ETIM classification

ETIM 8	EC000058
--------	----------

Accessories



10011011
Mounting plate for 01.162609



10027001
HINGE EXTERNAL / GREY



10061424
DIN rail 35/7,5 for xx.162609



10062005
Earth rail for 01.162609