



27030300

## Handheld Enclosure Limanda

311 x 281 x 72 mm

Handheld Enclosure Limanda 311 x 281 x 72 mm

[Catalogues](#)[Assembly instructions](#)[Declaration of Conformity](#)[Drawing](#)[3D Data](#)

## Technical data

Height	311 mm
Width	281 mm
Depth	72 mm
Material	Polyamide 6 (PA6)
Colour	black-grey (RAL 7021)
Ingress protection	IP65
Degree of protection norm	EN 60529
temperature min.	-20 °C
temperature max.	60 °C
Seal material	CR-(Chloroprene)
Surface resistance	10 <sup>12</sup> Ohm

## Commercial data

Country of origin	HU
Order unit	1 Piece
Customs tariff number	39269097
Weight	0.9 kg
GTIN	4250157917249














## ETIM classification

ETIM 8	EC001031
--------	----------

ROSE SYSTEMTECHNIK GMBH  
Erbeweg 13-15  
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0  
Fax: +49 571 50 41-6  
Mail: [rose@rose-pw.de](mailto:rose@rose-pw.de)

## Accessories

	<b>27030071</b> Limanda I Handle incl. Z-Taster right		<b>27030072</b> Limanda I Handle incl. Z-Taster left
	<b>27030083</b> Limanda I Handle		<b>27030084</b> Limanda Mounting system
	<b>27030085</b> Limanda Carrying strap		<b>27030086</b> Limanda I Quiver
	<b>27030090</b> Limanda I Quiver with Intermediate frame		<b>27030092</b> Limanda Carrying strap 2
	<b>27030380</b> Limanda I Front plate		<b>27030381</b> Limanda I Intermediate frame
	<b>50020005</b> Inclining adapter Inclining adapter		<b>50020006</b> Inclining adapter Inclining adapter
	<b>50020007</b> Inclining adapter Inclining adapter		